Appia Life 2 Group

Installation Requirements



| |Water

• 3/8" dedicated cold water line with shut-off valve

and compression fitting. Provided by:

Water hardness 3gpg or 50 ppm. Voltage Coffee Supply
Line pressure 2-4bar, cold water. voltagecoffeesupply.com
Water flow rate Minimum 1 GPM info@voltagesupply.com
Filtration 500 ppm. Voltage Coffee Supply
Minimum 1 GPM info@voltagesupply.com
800-269-0051
25tiof of top 200

Filtration ≤ 1.0 micron Free Shipping - Satisfaction Guaranteed!
TDS 50-250 ppm

Alkalinity 10-150 ppm
Chlorine ≤ 0.50 ppm
PH 6.5-8.5



• Volts: 220 (range of 208-240)

Watts: 3400Amp draw: 17

• Receptacle: Nema 6-20


Drain

• Open gravity drain of minimum 1.25 inch I.D., within 4 feet of the machine.

Counter Space

Height: 20 inchesDepth: 21 inchesWidth: 31 inches

Countertop Drain Hole Location











Nema 6-20 (receptacle)





I, the customer, understand that these requirements must be in when the installer arrives. Failure to have the site ready will result in additional service and travel charges, and may cause further delays in installation.		
Customer Name:	Signa	ature:
Company Name:		
Phone:	Email:	Reference number:



